

EJ Company

CRONUS

Diameter Range:
25.00 - 65.00 MM
.984-2.559 INCH





Note:

1. Drills can be ordered in an FL pad variant by using product code EJ-CRONUS-FL.

CR Pad Example : EJ-CRONUS D1.000 STS 803

FL Pad Example : EJ-CRONUS-FL D1.000 STS803

**Each drill only has one pad style.

Diameter range, inch	Tube range	Ordering code, Drill head	Inserts				
			Central	Intermediate	Peripheral	FL Pad	CR Pad
.984-1.039	03	EJ-CRONUS DX.XXX STS803	EJCR-050308M-C	EJCR-050308M-I	EJCR-060308H-P	EJ-FL6.4R2SCIS	EJ-CR06
1.040-1.099	04	EJ-CRONUS DX.XXX STS804	EJCR-050308M-C	EJCR-050308M-I	EJCR-060308H-P	EJ-FL6.4R2SCIS	EJ-CR06
1.100-1.129	04	EJ-CRONUS DX.XXX STS804	EJCR-050308M-C	EJCR-050308M-I	EJCR-060308H-P	EJ-FL6.4SCIS	EJ-CR06
1.130-1.220	05	EJ-CRONUS DX.XXX STS805	EJCR-06T308M-C	EJCR-050308M-I	EJCR-060308H-P	EJ-FL6.4SCIS	EJ-CR06
1.221-1.311	06	EJ-CRONUS DX.XXX STS806	EJCR-06T308M-C	EJCR-06T308M-I	EJCR-08T308H-P	EJ-FL07SCIS	EJ-CR07
1.312-1.338	07	EJ-CRONUS DX.XXX STS807	EJCR-06T308M-C	EJCR-06T308M-I	EJCR-08T308H-P	EJ-FL07SCIS	EJ-CR07
1.339-1.378	07	EJ-CRONUS DX.XXX STS807	EJCR-08T308M-C	EJCR-06T308M-I	EJCR-08T308H-P	EJ-FL07SCIS	EJ-CR07
1.379-1.425	07	EJ-CRONUS DX.XXX STS807	EJCR-08T308M-C	EJCR-08T308M-I	EJCR-08T308H-P	EJ-FL07SCIS	EJ-CR07
1.426-1.495	08	EJ-CRONUS DX.XXX STS808	EJCR-08T308M-C	EJCR-08T308M-I	EJCR-08T308H-P	EJ-FL07SCIS	EJ-CR07
1.496-1.535	08	EJ-CRONUS DX.XXX STS808	EJCR-08T308M-C	EJCR-08T308M-I	EJCR-08T308H-P	EJ-FL08SCIS	EJ-CR07
1.536-1.559	08	EJ-CRONUS DX.XXX STS808	EJCR-08T308M-C	EJCR-08T308M-I	EJCR-09T308H-P	EJ-FL08SCIS	EJ-CR07
1.560-1.692	09	EJ-CRONUS DX.XXX STS809	EJCR-08T308M-C	EJCR-08T308M-I	EJCR-09T308H-P	EJ-FL08SCIS	EJ-CR08
1.693-1.771	10	EJ-CRONUS DX.XXX STS810	EJCR-10T308M-C	EJCR-08T308M-I	EJCR-09T308H-P	EJ-FL08SCIS	EJ-CR08
1.772-1.850	10	EJ-CRONUS DX.XXX STS810	EJCR-10T308M-C	EJCR-08T308M-I	EJCR-09T308H-P	EJ-FL10SCIS	EJ-CR08
1.851-1.968	11	EJ-CRONUS DX.XXX STS811	EJCR-12T308M-C	EJCR-08T308M-I	EJCR-09T308H-P	EJ-FL10SCIS	EJ-CR10
1.969-2.035	11	EJ-CRONUS DX.XXX STS811	EJCR-10T308M-C	EJCR-08T308M-I	EJCR-11T308H-P	EJ-FL10SCIS	EJ-CR10
2.036-2.165	12	EJ-CRONUS DX.XXX STS812	EJCR-10T308M-C	EJCR-08T308M-I	EJCR-11T308H-P	EJ-FL10SCIS	EJ-CR10
2.166-2.213	12	EJ-CRONUS DX.XXX STS812	EJCR-10T308M-C	EJCR-12T308M-I	EJCR-11T308H-P	EJ-FL10SCIS	EJ-CR12
2.214-2.283	13	EJ-CRONUS DX.XXX STS813	EJCR-10T308M-C	EJCR-12T308M-I	EJCR-11T308H-P	EJ-FL10SCIS	EJ-CR12
2.284-2.361	13	EJ-CRONUS DX.XXX STS813	EJCR-12T308M-C	EJCR-12T308M-I	EJCR-11T308H-P	EJ-FL10SCIS	EJ-CR12
2.362-2.559	13	EJ-CRONUS DX.XXX STS813	EJCR-12T308M-C	EJCR-12T308M-I	EJCR-11T308H-P	EJ-FL14SCIS	EJ-CR12